

MAR901 series Pilot operated


AIR UNITS (R. UNIT)



mindman



Symbol



- MAR901 can be installed at any point in the compressed air system without regard to accessibility ensuring accurate pressure regulation over a wide range of air flows upto 56640 l/min

Specification

Model	MAR901
Bore No.	50A
Port size	2
Medium	Air
Max. operating pressure	3.1 MPa
Regulated pressure range	Upto 1.75MPa (with the help of a pilot regulator)
Ambient temperature	0~+80°C (No freezing)
Standard nominal flow rate (※)	59000 l/min
Attachment	Pressure gauge (PG-50)
Weight	3055 g

Order example

MAR901 — 50A — □

MODEL

BORE SIZE
50A: 2

PORT THREAD
Blank: Rc thread
G: G thread
NPT: NPT thread

※ Flow is at 1 MPa supply pressure and 0.1 MPa pressure drop of 0.6 MPa of secondary pressure.

Pilot operation

