

M* 系列



2口2位 / 3口2位電磁閥

mindman

電磁閥 / 選用表：

※ 止漏墊圈代號：N NBR, J EPDM, V VITON, P PTFE, T TEFLON, R RUBY, Z FFKM, S Silicon

2
口
2
位

型號	內部構造			常閉	常開	適用流體								材質		配管口徑	CV值	型錄頁次
	活塞	膜片	柱塞			水、空氣	熱水	水蒸氣	輕油	重油	瓦斯	真空	本體	止漏墊圈				
MBS			○	●		●			●		●	●	黃銅	N,J,V,T	1/8,1/4	0.03~0.18	2-3	
MBD			○	●		●			●		●	●	鋼	N,V	1/4~1/2	0.14~0.95	2-4	
MCS			○	●		●			●		●	●	黃銅	N,J,V,T,Z,R	1/4~3/4	0.12~1.30	2-5	
MED		○		●		●							鍛造銅	N	1/4~1/2	1.8~2.2	2-7	
MEP			○	●		●							鍛造銅	N	3/8,1/2	1.8~2.2	2-8	
MGA	○			●		●	●						鍛造銅	N,J,V	3/8,1/2	1.9~2.6	2-9	
MGS	○			●		●	●	●					鍛造銅	T	3/8,1/2	1.9~2.6	2-9	
MGD		○		●		●				●			鍛造銅	N,J,V	3/8~2	2.0~31	2-10	
MJS			○	●		●			●	●	●		黃銅	N,J,V	—	0.10~0.42	2-11	
MJR			○	●		●			●	●	●		黃銅	N,J,V	—	0.10~0.42	2-11	
MPD		○		●		●							塑膠(尼龍)	N,J,V	1/2~1	4~11	2-13	
MPK		○		●		●							塑膠(尼龍)	N,J,V	1/2~1	4~11	2-13	
MRB			○		●	●			●	●			黃銅	N,J,V	1/8,1/4	0.05~0.09	2-14	
MRC			○		●	●			●	●			黃銅	N,J,V	1/8~3/8	0.10~0.31	2-14	
MUSC			○	●		●			●	●	●		不銹鋼#303	N,J,V,Z,T,R	1/8~3/8	0.03~1.30	2-15	
MUSD		○		●		●			●	●			不銹鋼#304	N,J,V	1/2	2.0	2-16	
MWA	○			●		●			●	●			黃銅	N	3/8~2	3.0~31	2-19	
MWH	○			●					●				黃銅	V	3/8~2	3.0~31	2-19	
MWS	○			●		●	●						黃銅	T	3/8~2	3.0~31	2-19	
MWD		○		●		●				●			鍛造銅	N,J,V	3/8~2	3.0~31	2-21	
MWK		○		●		●				●			鍛造銅	N,J,V	3/8~2	3.0~31	2-21	
MYA	○			●		●	●						鍛造銅	N,J,V	3/8,1/2	1.9~2.6	2-22	
MYS	○			●		●	●	●					鍛造銅	T	3/8,1/2	1.9~2.6	2-22	
MZS			○	●		●			●	●			鍛造銅	N,J,V,Z	3/8~3/4	0.12~0.83	2-23	
MUD			○	●	●	●			●	●			鍛造銅	N,V,S,P	1/8~3/8	0.23~0.58	2-27	
MUS-8/10	○			●				●					鍛造銅	P	1/4,3/8	0.23~0.58	2-27	
MUDC		○		●		腐蝕性流體						PVC/PTEF	N	1/4~1	0.28~4	2-29		
MSUS	○			●	●	●			●		●	●	不銹鋼#316	N,V,S,P	1/8~2	0.23~48	2-30	
MUAO	○			●		●			●				黃銅	N	1/4~1/2	2.5	2-32	
MUW		○		●		●			●				鍛造銅	N,V,S	3/8~2	2.4~48	2-33	
MUW-NO		○		●	●	●				●	●		鍛造銅	N,V,S	3/8~2	4.5~48	2-34	
MUW-F		○		●	●	●							鑄鐵FC-20	N	1 1/4~4	22~180	2-35	
MUG		○		●						●			鍛造銅	N	3/8~2	2.4~48	2-36	
MUV		○		●							●		鍛造銅	N	3/8~2	2.4~48	2-36	
MUAW	○			●		●							鑄造銅	N	1/2~2	4~48	2-37	
MUS	○			●		●			●	●			鑄造銅	P	1/2~2	17~50	2-38	
MUS-F	○			●		●			●	●			鑄鐵FC-20	P	1 1/4~4	22~175	2-38	
MSUW		○		●	●	●			●		●		不銹鋼#316	N,V,S	1/2~2	4.5~48	2-39	
MSUW-F		○		●	●	●			●		●		不銹鋼#316	N,V,S	1/2~2	4.5~48	2-40	
MUPS	○			●		●			●	●			鍛造銅	P	1/2~1	4~12	2-41	
MXAD			○	●		●			●	●	●		鍛造銅	N,J,V,S	3/8~1/2	0.26~0.97	2-42	
MXAD-AF		○		●		●			●	●	●		鍛造銅	N,J,V,S	3/8~2	4.5~48	2-43	
MXBD			○	●		●			●	●	●		鍛造銅	N,J,V,S	3/8~1/2	0.23~0.79	2-44	
MXCD		○		●		●			●				鍛造銅	N,V	3/8~1/2	2.4~2.7	2-45	
MPV		○		●		●			●				鍛造銅	N,J,V,S	3/8~1/2	4.5~9.3	2-46	

3
口
2
位

型號	內部構造			常閉	常開	適用流體								材質		配管口徑	CV值	型錄頁次
	活塞	膜片	柱塞			水、空氣	熱水	水蒸氣	輕油	重油	瓦斯	真空	本體	止漏墊圈				
MCT			○	●		●					●	●	黃銅	N,V	1/4~3/4	0.10~0.80	2-6	
MJT			○	●		●			●		●	●	黃銅	N,J,V	—	0.10~0.42	2-11	
MRJ			○		●	●			●	●	●		黃銅	N,J,V	—	0.10~0.31	2-11	
MUST			○	●		●			●	●	●		不銹鋼#303	N,V	1/8~3/8	0.02~0.80	2-17	
MUT			○	●	●	●			●	●	●		鍛造銅	V	1/8~3/8	0.02~0.31	2-18	
MZT			○	●		●			●	●	●		鍛造銅	N,J,V,Z	1/8~3/4	0.08~0.80	2-24	
MUA			○	●		●			●		●		鍛造銅	N	1/4,3/8	0.1~0.12	2-28	