
BN-2501 系列


空氣調理組合(三點組合)

NISCON * D 4 H A H

BN-2501(20A)




BN-2501(25A)



外觀尺寸:


BN-2501-20A




規格:

型號	BN-2501	
配管口徑代號	20A	25A
配管口徑尺寸	Rc3/4	Rc1
使用流體	空氣	
使用壓力範圍	1 MPa 以下	
耐壓力	1.5 MPa	
設定壓力範圍	0.1~0.85 MPa	
周圍溫度	-5~+60℃ (不凍結)	
重量Kgf	4.2	
儲油量	400	
壓力計	標準裝備	

流量特性:





BN-2501-25A

