AIR UNIT (FILTER)



• Ideally suited for header lines and very high flow applications.

contaminants to protect air tools and equipment.



Symbol

Manual drain



Auto drain



Specification

Model	MAF901
Bore No.	50A
Port size	2
Medium	Air
Operating pressure range (%1)	0.05~1.75 MPa
Ambient temperature	0~+80°C (No freezing)
Filter element	Standard: 50 μ m
Standard nominal flow rate (%2)	63000 ∉min
Weight	6930 g

- ※2. Flow is at pressure P= 0.6 MPa with purssure drop △P=0.1 MPa.

Order example



