


# MAL302 series

## AIR UNIT (FILTER)



### Symbol



### Specification

Model	MAL302		
Bore No.	8A	10A	15A
Port size	1/4	3/8	1/2
Medium	Air		
Max. operating pressure	1 MPa		
Proof pressure	1.5 MPa		
Ambient temperature	-5~+60°C (No freezing)		
Lubricating oil capacity	65 c.c		
Min. flow for oil drip	50 ℓ/min	60 ℓ/min	
Recommended lubricating oil	Turbine oil ISO-VG32		
Weight	345 g		

### Order example

MAL302 — 8A — □ — B — □

MODEL

BORE SIZE  
8A: 1/4  
10A: 3/8  
15A: 1/2

Blank: PC bowl  
N: Nylon bowl

B: C type  
bracket

PORT THREAD  
Blank: Rc thread  
G: G thread  
NPT: NPT thread

### Option accessories

#### C type bracket

