

MVHA-4* series

HAND VALVE



Mindman



Specification

Model	MVHA-4V	MVHA-4P	MVHA-4PP
Bore No.	M5		
Port size	M5×0.8		
No. of port	5		
No. of position	2		
Medium	Air		
Operating pressure range	0~0.9 MPa		
Effective orifice	1.9 mm ²		
Ambient temperature	-5~+60℃ (No freezing)		
Weight	62g	61g	66g

Order example

MVHA - 4 V

MODEL

4: 4way(5port)

V: V toggle
P: Single push button
PP: Double push button

MVHA-4V

MVHA-4P

MVHA-4PP

