



Order example

TPU0503 — 200 — B

MODEL

EACH ROLL
(m)

COLOR

- B: Black
- BU: Blue
- O: Orange
- G: Green
- Y: Yellow
- T: Transparent

Specification

Model	TPU*
Medium	Air
Operating pressure range	0~100 psi (0~0.7MPa)
Working vacuum	- 29.5in.Hg (- 100kPa)
Ambient temperature	- 5~+ 140°F (- 15~+ 60°C) (No freezing)

Taiwan made PU tube

Model	ID × OD (mm)	Each roll (m)	Available color
TPU0420	2 × 4	200	B, BU, O, T
TPU0425	2.5 × 4	200	B, BU, O, G, Y, T
TPU0503	3 × 5	200	B, BU, O, G, Y, T
TPU0604	4 × 6	200	B, BU, O, G, Y, T
TPU0850	5 × 8	100	B, BU, O, G, Y, T
TPU0806	6 × 8	100	B, BU, O, G, Y, T
TPU0906	6.5 × 9.5	200	B, BU, O, G, Y, T
TPU1065	6.5 × 10.0	100	B, BU, O, G, Y, T
TPU1108	8.0 × 11	100	B, BU, O, G, Y, T
TPU1208	8.0 × 12.0	100	B, BU, O, G, Y, T
TPU1296	9.6 × 12.7	100	B, BU, O, G, Y, T
TPU1613	13 × 16	100	B, BU, O, G, Y, T

Available color

- Black(B), ● Blue(BU), ● Orange(O), ● Green(G), ● Yellow (Y),
- Transparent(T)