












### 搭配選用表：

●：標準型    ○：外牙型 (代號:M1,M2,N1,N2)  
 ◎：另加購轉接頭(安裝於T8 / T10支架)

型號		壓力傳感器		高精度數位壓力傳感器					壓力傳感器
		MP1	MP10	MP30	MP41	MP43	MP45	MP50	MPS
圖示									
型號	接續口徑	R1/8	R1/8	R1/8	R1/8	R1/8	R1/8	R1/4	R1/8
MACP200	Rc1/8					●	●		
MACP300※	Rc1/8	◎	◎	◎		●	●		◎
MACP302	Rc1/8				●	●	●		
MACP400	Rc1/4							●	
MACP401	Rc1/8	◎	◎	◎	●	●	●		●
MACP402	Rc1/4							●	
MACP403	Rc1/8	◎	◎	◎	●	●	●		●
MACP500	Rc1/4							●	
MAcc300	Rc1/8					●	●		
MACT300※	Rc1/8	◎	◎	◎		●	●		◎
MACT302	Rc1/8				●	●	●		
MACT400	Rc1/4							●	
MACT401	Rc1/8	◎	◎	◎	●	●	●		●
MACT402	Rc1/4								
MACT403	Rc1/8	◎	◎	◎	●	●	●		●
MACT500	Rc1/4							●	
MAFR200	Rc1/8					●	●		
MAFR300※	Rc1/8					●	●		
MAFR302	Rc1/8				●	●	●		
MAFR400	Rc1/4							●	
MAFR401	Rc1/8				●	●	●		
MAFR402	Rc1/4							●	
MAFR403	Rc1/8				●	●	●		
MAFR500	Rc1/4							●	
MAR200	Rc1/8					●	●		
MAR300	Rc1/8					●	●		
MAR301	Rc1/8					●	●		
MAR302	Rc1/8				●	●	●		
MAR400	Rc1/4							●	
MAR401	Rc1/8					●	●		
MAR402	Rc1/4				●			●	
MAR403	Rc1/8					●	●		
MAR500	Rc1/4				●			●	

※ 300L 規格與 300 系列相同

### 搭配選用表：

型號		數位式壓力錶		壓力錶
		MP23	MPG-60	PG
圖示				
型號	接續口徑	R/Rc1/8	R1/8;1/4	R1/8;1/4
MACP200	Rc1/8	○	●	●
MACP300※	Rc1/8	○	●	●
MACP302	Rc1/8	○	●	●
MACP400	Rc1/4	○	●	●
MACP401	Rc1/8	○	●	●
MACP402	Rc1/4	○	●	
MACP403	Rc1/8	○	●	●
MACP500	Rc1/4	○	●	
MAcc300	Rc1/8	○	●	●
MACT300※	Rc1/8	○	●	●
MACT302	Rc1/8	○	●	●
MACT400	Rc1/4	○	●	●
MACT401	Rc1/8	○	●	●
MACT402	Rc1/4	○	●	
MACT403	Rc1/8	○	●	●
MACT500	Rc1/4	○	●	
MAFR200	Rc1/8	○	●	●
MAFR300※	Rc1/8	○	●	●
MAFR302	Rc1/8	○	●	●
MAFR400	Rc1/4	○	●	●
MAFR401	Rc1/8	○	●	●
MAFR402	Rc1/4	○	●	
MAFR403	Rc1/8	○	●	●
MAFR500	Rc1/4	○	●	
MAR200	Rc1/8	○	●	●
MAR300	Rc1/8	○	●	●
MAR301	Rc1/8	○	●	●
MAR302	Rc1/8	○	●	●
MAR400	Rc1/4	○	●	●
MAR401	Rc1/8	○	●	●
MAR402	Rc1/4	○	●	
MAR403	Rc1/8	○	●	●
MAR500	Rc1/4	○	●	

※ 300L 規格與 300 系列相同

### 外牙型 / 訂購代號：

