












● : Standard type ○ : Male thread type (Code: M1, M2, N1, N2)
 ◎ : In addition order joint bush (Install in module mounting bracket)

Selector table

Model		Pneumatic pressure switch		High precision digital pressure switch					Pneumatic pressure switch
		MP1	MP10	MP30	MP41	MP43	MP45	MP50	MPS
Pictures									
Model	Port size	R1/8	R1/8	R1/8	R1/8	R1/8	R1/8	R1/4	R1/8
MACP200	Rc1/8					●	●		
MACP300*	Rc1/8	◎	◎	◎		●	●		◎
MACP302	Rc1/8				●	●	●		
MACP400	Rc1/4							●	
MACP401	Rc1/8	◎	◎	◎	●	●	●		●
MACP402	Rc1/4							●	
MACP403	Rc1/8	◎	◎	◎	●	●	●		●
MACP500	Rc1/4							●	
MACC300	Rc1/8					●	●		
MACT300*	Rc1/8	◎	◎	◎		●	●		◎
MACT302	Rc1/8				●	●	●		
MACT400	Rc1/4							●	
MACT401	Rc1/8	◎	◎	◎	●	●	●		●
MACT402	Rc1/4								
MACT403	Rc1/8	◎	◎	◎	●	●	●		●
MACT500	Rc1/4							●	
MAFR200	Rc1/8					●	●		
MAFR300*	Rc1/8					●	●		
MAFR302	Rc1/8				●	●	●		
MAFR400	Rc1/4							●	
MAFR401	Rc1/8				●	●	●		
MAFR402	Rc1/4							●	
MAFR403	Rc1/8				●	●	●		
MAFR500	Rc1/4							●	
MAR200	Rc1/8					●	●		
MAR300	Rc1/8					●	●		
MAR301	Rc1/8					●	●		
MAR302	Rc1/8				●	●	●		
MAR400	Rc1/4							●	
MAR401	Rc1/8					●	●		
MAR402	Rc1/4				●			●	
MAR403	Rc1/8					●	●		
MAR500	Rc1/4				●			●	

* 300L specification is the same as the 300 series.

Selector table

Model		Digital pressure gauge		Pressure gauge
		MP23	MPG-60	PG
Pictures				
Model	Port size	R/Rc1/8	R1/8;1/4	R1/8;1/4
MACP200	Rc1/8	○	●	●
MACP300*	Rc1/8	○	●	●
MACP302	Rc1/8	○	●	●
MACP400	Rc1/4	○	●	●
MACP401	Rc1/8	○	●	●
MACP402	Rc1/4	○	●	
MACP403	Rc1/8	○	●	●
MACP500	Rc1/4	○	●	
MAcc300	Rc1/8	○	●	●
MACT300*	Rc1/8	○	●	●
MACT302	Rc1/8	○	●	●
MACT400	Rc1/4	○	●	●
MACT401	Rc1/8	○	●	●
MACT402	Rc1/4	○	●	
MACT403	Rc1/8	○	●	●
MACT500	Rc1/4	○	●	
MAFR200	Rc1/8	○	●	●
MAFR300*	Rc1/8	○	●	●
MAFR302	Rc1/8	○	●	●
MAFR400	Rc1/4	○	●	●
MAFR401	Rc1/8	○	●	●
MAFR402	Rc1/4	○	●	
MAFR403	Rc1/8	○	●	●
MAFR500	Rc1/4	○	●	
MAR200	Rc1/8	○	●	●
MAR300	Rc1/8	○	●	●
MAR301	Rc1/8	○	●	●
MAR302	Rc1/8	○	●	●
MAR400	Rc1/4	○	●	●
MAR401	Rc1/8	○	●	●
MAR402	Rc1/4	○	●	
MAR403	Rc1/8	○	●	●
MAR500	Rc1/4	○	●	

* 300L specification is the same as the 300 series.

Order example of male thread type

