

METS 系列 規格索引

滑台電動缸-螺桿驅動 (不附馬達)



METS 滑台電動缸：

使用環境	傳動方式	型號	馬達尺寸 (W)	本體寬幅 (mm)	位置重複精度 (mm)	螺桿規格(C7級)		最大可搬重量(kg)		最高速度※1 (mm/s)
						外徑 (mm)	導程 (mm)	水平使用 (mm)	垂直使用 (mm)	
一般環境	滾珠螺桿	METS-5M	42M (步進馬達)	51	±0.01	12	2	10	7	16
							5	10	3	41
							10	5	1.5	83
			100W	51	±0.01	12	2	10	7	100
							5	10	3	250
							10	5	1.5	500
		METS-6M	57M (步進馬達)	65	±0.01	12	2	30	15	16
							5	30	10	41
							10	15	5	83
			100W	65	±0.01	12	2	30	15	100
							5	30	10	250
							10	15	5	500
		METS-10	100W	102	±0.01	16	5	50	12	250
							10	30	8	500
							16	22	5	800
							20	18	3	1000
		METS-12	100W	102	±0.01	16	5	50	12	250
							10	30	8	500
							16	22	5	800
							20	18	3	1000
		METS-13	200W	135	±0.01	16	5	70	17	250
							10	47	12	500
							16	30	6	800
							20	24	4	1000
							5	95	27	250
							10	75	18	500
		METS-14	200W	135	±0.01	16	16	44	7	800
							20	35	6	1000
							5	110	33	250
			400W	135	±0.01	16	10	88	22	500
							16	48	10	800
							20	40	8	1000
		METS-17	400W	170	±0.01	20	5	120	40	250
							10	110	30	500
							20	75	14	1000
							40	35	7	2000
750W	170		±0.01	20	5	120	50	250		
					10	120	40	500		
					20	83	25	1000		
					40	50	10	2000		
METS-22	750W	220	±0.01	25	5	150	55	250		
				25	10	150	45	500		
				25	25	120	20	1250		
				20	40	60	10	2000		

※1. 最高速度(mm/s)是以伺服馬達最高轉速3000rpm為基準，步進馬達最高轉速500rpm為基準。

