









Mounting style






B: Panel mounting style

S: Plug mounting style

Order example



Со	de	Symbol	Description					
1	0		Single acting / Normally returned without thread					
1 5			Single acting / Normally returned male thread					

Features

A short stroke miniature cylinder with a shorter overall length.

The installation space can be significantly reduced because this cylinder can be recessed directly into a machine body or installed on a panel. Thus, the machines can be made more compact.

Specification

Mod	lel	MCMJPB MCMJPS					
Acting type		Single acting					
Tube I.D. (mm)		6	1	0	15		
Medium			А	ir			
Max. operating p	ressure	0.07 MPa					
Min. operating	φ6	0.2 MPa					
pressure	φ 10,15	0.15 MPa					
Proof pressure		1 MPa					
Ambient tempera	ature	-5~+60°C (No freezing)					
Lubricator		Not required					
Available speed	range	50~500 mm/sec					
Max. allowableb	kinetic energy	0.003J 0.008J 0.019J					

^{*} All this product line is without magnet.

Table for standard stroke

Tube I.D.	Stroke (mm)
φ 6,10,15	5,10,15

Spring retracting force

Unit: N

Tube I.D.	Extended position	Retracted position
φ 6	3.92	1.42
φ 10	5.98	2.45
φ 15	10.80	4.41

Theoretical force


Unit: N


Tube I.D.	Operation	Operat	ing Pressure	(MPa)			
Tube I.D.	direction	0.3	0.5	0.7			
φ6	OUT	4.56	10.2	15.9			
φυ	IN	1.42					
φ10	OUT	17.6	33.3	49.0			
φισ	IN		2.45				
φ15	OUT	42.2	113				
ΨΙΟ	IN		4.41				




PEN CYLINDER


MCMJPB






MCMJPS






Code	В	٦	Е		F		G	ш	K	мм	NN	Q	ь		S		w		Z								
Tube I.D.	А	В	C	_	5st	10st	15st	G	" '	"	-	П	п	"	"	^	IVIIVI	1414	¥	, ,	5st	10st	15st	•	5st	10st	15st
6	7	12	13.9	6	12.5	19.5	26.5	8.5	9	3.5	M3×0.5	M10×1.0	3	9	18.5	25.5	32.5	3	27.5	34.5	41.5						
10	10	19	22	6	14.5	21	28	12	12	3.5	M4×0.7	M15×1.5	5	13	20.5	27	34	4	32.5	39	46						
15	12	27	31	7	16.5	22.5	29	19	14	4.2	M5×0.8	M22×1.5	6	20	23.5	29.5	36	5	37.5	43.5	50						

Inside structure & Parts list



No.	Part name		Material					
INO.	Fait name	6	10	16				
1	Body		Copper					
2	Cover		Copper					
3	Piston rod	Stainless steel						
4	Piston packing	NBR						
5	Spring	SWP						
6	Nut	Copper Carbon steel						
7	Rod front nut	Carbon steel						



When plug mounting

Maching dimension for mounting

Tube I.D.	Code Stroke	Α	В	С	D	Е	F	G
	5	16	12.5	10				
6	10	23	19.5	17	3.5	3.5 M10×1.0		3
	15	30	26.5	24				
	5	17	13.5	10.5		M15×1.5	12	4
10	10	23.5	20	17	3.5			
	15	30.5	27	24				
	5	19	14.5	11.5				
15	10	25	20.5	17.5	4.5 M22×1.5		19	5
	15	15 31.5	27	24				

