MAF900 series

AIR UNIT (FILTER)







Symbol

Manual drain



Auto drain




- Removing upto 99% of the liquid water.
- Design of the filter elements gives both surface and depth filtration for cleaner air.
- Ideally suited for header lines and large flow rated tools and cylinder operations.

Specification

Model	MAF900
Bore No.	40A
Port size	1 1/2
Medium	Air
Operating pressure range (%1)	0.05~1.75 MPa
Ambient temperature	0~+80°C (No freezing)
Filter element	Standard: 50 μ m
Standard nominal flow rate (%2)	20000 ∉/min
Weight	2035 g

- ※2. Flow is at pressure P= 0.6 MPa with pressure drop△P=0.1 MPa.

Order example



Blank: Manual drain D: Auto drain

