


MAFR100 series

AIR UNIT (F.R.UNIT)



Symbol




Specification

Model	MAFR100
Port size	M5×0.8
Medium	Air
Operating pressure range	0.05~1 MPa
Proof pressure	1.5 MPa
Regulated pressure range	0.05~0.7 MPa
Ambient temperature	-5~+60°C (No freezing)
Filter element	Standard: 5 μm Option: 40 μm
Attachment	Pressure gauge (PG-25), bracket
Weight	130 g

Order example

MAFR100 — M5 — □

MODEL PORT SIZE FILTER ELEMENT
Blank: 5 μm
40u: 40 μm



Flow feature

