

MAR900 series

AIR UNIT (R.UNIT)




- MAR900 reducing the system pressure to a desired level and maintain it at a constant level despite change in inlet pressure and changes in downstream flow requirements.

Specification

Model	MAR900
Bore No.	40A
Port size	1 1/2
Medium	Air
Max. operating pressure	2.1 MPa
Regulated pressure range	0.09~0.86 MPa
Ambient temperature	0~+80°C (No freezing)
Standard nominal flow rate (※)	11000 ℓ/min
Attachment	Pressure gauge (PG-50)
Weight	1208 g

Symbol



Order example

MAR900 — 40A — □

MODEL

BORE SIZE
40A: 1 1/2

PORT THREAD
Blank: Rc thread
G: G thread
NPT: NPT thread

※ Flow is at 1 MPa supply pressure and 0.1 MPa pressure drop of 0.6 MPa of secondary pressure.

