

高性能快速排氣閥

Humphrey

進口代理商品

快速型

規格：

型號	SQE (TAC級)	SQE1	SQE2	QE2	QE3	QE4	QE5	
進氣口in	10-32UNF(內牙)	1/8"	1/4"	1/4"	3/8"	1/2"	3/4"	
配管口徑	輸氣口out	10-32UNF(內牙)	1/8"	1/4"	1/4"	3/8"	1/2"	
	排氣口exh.	10-32UNF(外牙)	1/4"	1/4"	3/8"	3/8"	3/4"	
使用流體	空氣							
使用壓力範圍	MIN	0.02	0.03	0.03	0.02	0.014	0.007	
	MAX	0.86	1.07					
周圍溫度		-7~+65°C		-30~+80°C				
油潤滑	不需要							
充/排氣	壓力	(A)0.026	(A)0.036	(A)0.027	(B)0.170	(B)0.130	(C)0.537	
時間sec.※	供給	(A)0.030	(A)0.022	(A)0.021	(B)0.160	(B)0.100	(C)0.440	
	排氣						(C)0.508	
	MPa						(C)0.417	

※ 空氣量需求：「A」表164cc，「B」表1640cc，「C」表16400cc


大氣壓下之空氣流量：

型號	SQE (TAC級)	SQE1	SQE2	QE2	QE3	QE4	QE5
0.2 MPa	76.0	636.8	905.6	1273.5	1556.5		
0.35 MPa	113.0	948.1	1330.1	1839.5	2264.0		
0.55 MPa	198.0	1443.3	1981.0	2716.8	3537.5		
0.7 MPa	232.0	1782.9	2405.5	3396.0	4386.5		
0.85 MPa		2122.5	2943.2	4245.0	5377.0		

訂購代號：

例 **SQE1**

外觀尺寸：




mm


代號	A	B	C	D	E	F	G	H	J	K	L
SQE	此型尺寸在圖片旁										
SQE1, SQE2	27.7	13.9	20.5	30.9	42.4						
QE2, QE3	38.1	21.1	31.8	45.2	60.4	28.9	38.1	55.6	21.8	13.9	8.6
QE4, QE5	55.4	28.9	45.9	70.6	70.6	37.5	50.8	69.8	33.7	15.4	6.8

※ 屬固定座之尺寸代號

作動型式：



SQE



SQE1

1/8 Pipe




SQE2

1/4 Pipe



QE2

1/4 Pipe



QE3

3/8 Pipe



QE4

1/2 Pipe



QE5

3/4 Pipe

